

EVO-STIK Mirror Adhesive

A SOLVENT FREE SMP POLYMER ADHESIVE

Date: 11 December 2015 Fact Sheet No.: TDS00822

YOUR SMART ADVANTAGES	
- Solvent-free SMP polymer adhesive	
. ,	
- Permanently elastic	
– Adjustable with high initial grab	

USES

EVO-STIK Mirror Adhesive is a specially formulated SMP polymer permanently elastic adhesive designed for bonding all sizes of mirror. A bonded mirror is safer because there is no risk of large pieces of glass falling, in the event of breakage.

EVO-STIK Mirror Adhesive can be used to bond mirrors to: sound plaster, concrete, wood, doors, ceramic tiles and also sloping walls and ceilings (see method of use).

PRODUCT CHARACTERISTICS		
Colour	Light Grey	
Form	Slump resistant paste	
Specific Gravity	1.4 approx.	
Composition	SMP polymer	
Product Code	30132230 290ml x 12	
Storage/Shelf Life	Store for up to 18 months from date of manufacture when stored in original, unopened packaging under cool, dry conditions within the temperature range of +5°C to +30°C.	

TYPICAL PERFORMANCE DATA (Approx.)		
Adhesion	Excellent to most common building substrates that are clean and dry	
Skinning Time	15 minutes approx. at 20°C	
Tack Free Time	20 minutes approx. at 20°C	
Cure Rate	2mm – 3mm depth per 24 hours at 20°C	
Coverage	Approx. 10 lineal metres of 6mm diameter bead per 290ml cartridge	
	Coverage is dependent upon size, thickness and weight of mirror	

DIRECTIONS FOR USE

IMPORTANT: Before using EVO-STIK Mirror Adhesive refer to the relevant Health & Safety Data Sheet, available at www.bostik.co.uk.

PREPARATION

Substrate:

- The wall or ceiling should be clean, dry, dust and grease free
- 2. Ensure the surface is sound by removing any loose material and repairing unsound plaster.
- 3. On dusty porous surfaces prime first with a suitable primer check with Bostik Technical Services
- 4. If the substrate is subject to dampness fix battens to the wall and mount the mirror on these.

Mirror:

- 5. Clean the painted side of the mirror with methylated spirit.
- 6. Do not use EVO-STIK Mirror Adhesive if the mirror is backed with plastic safety film.



APPLICATION

Mirrors of 2mm and 4mm thickness on vertical walls:

- 7. Apply vertical beads of EVO-STIK Mirror Adhesive at 100mm intervals to the painted side of the mirror.
- 8. Mechanical fixing is not required.

Mirrors of 6mm and 8mm thickness and mirrors on sloping surfaces:

- 9. Apply vertical beads of EVO-STIK Mirror Adhesive at 30mm intervals to the painted side of the mirror.
- 10. Temporary mechanical support is essential.
- 11. Install the mirror within 10 minutes of applying the adhesive. Adjust as necessary then press the mirror firmly into place.
- 12. It is essential that air can circulate between the beads so that full cure can be attained as rapidly as possible. Heavier mirrors must be supported by self-adhesive pads, tape or battens until the adhesive has cured and is capable of supporting the load.

CLEANING

 Uncured adhesive may be removed using cloths lightly dampened with white spirit after carefully scraping off the bulk.

PRECAUTIONS IN USE

EVO-STIK Mirror Adhesive must not be used if the mirror is backed with plastic safety film. Do not bond to painted surfaces, due to the decorative surface being unable to support the load. Not suitable in areas directly adjacent to bitumen

For any application not covered please contact Technical Services on +44 (0)1785 272625 or visit www.bostik.co.uk for advice.

Recommendations and suggestions are for guidance only, since conditions of use are completely beyond our control.

For health and safety instruction, first aid measures and spillage and disposal instructions, see separate Health and Safety Data Sheet for EVO-STIK Mirror Adhesive, available at www.bostik.co.uk.





This disclaimer is issued by Bostik Limited ("the Company") and applies to the use of any products supplied by the Company ("the Products") displayed on this Technical Data Sheet ("TDS"). Please read this disclaimer carefully before using any of the Products. Using this TDS and/or the Product constitutes your acceptance of this disclaimer. Its contents shall prevail over any directions of use and any disclaimer and/or exclusion or limitation of liability of the Company which may appear on the packaging of the Products.

This disclaimer sets out the entire financial liability of the Company (including any liability for the acts or omissions of its employees, agents and sub-contractors) to any user of the Products ("Product User") in respect of any use made or resale by the Product User, of any of the Products in this TDS.

This disclaimer does not affect the Company's liability for death or personal injury arising from the Company's negligence in respect of the Products, nor its liability for fraud, or fraudulent misrepresentation, nor any other liability which cannot be excluded or limited under applicable law.

The Company's total liability however arising and whether caused by tort (including negligence and breach of statutory duty), breach of contract or otherwise, arising in connection with the use made or resale by the Product User of any of the Products in this TDS shall be limited to the price paid for the Product by the Product User.

The Company shall not be liable to the Product User for any pure economic loss, loss of profit, loss of business, depletion of goodwill or otherwise, in each case whether direct, indirect or consequential, or any claims (including in respect of personal injury insofar as not caused by the Company's negligence) for consequential compensation whatsoever (howsoever caused) which arise out of or in connection with the use made or resale by the Product User of any of the Products in this TDS.

The Company shall not be liable to the Product User in relation to any loss for any use which is inappropriate or use which is otherwise than in accordance with the relevant instructions for use of the Products in this TDS or on the Product. Product Users are advised to confirm the suitability of the Products by their own tests.

This TDS covers just one of a large range of products supplied by the Company.

Full information on these products and advice on application is freely available from our fully trained staff throughout the country. In addition, specialist technical advice is available from our Technical Services Department. This TDS supersedes all previous TDSs relating to the Products, and users of it must ensure that it is the current issue. Destroy all previous TDS, and if in any doubt, contact the Company, quoting the code number in the top right hand corner on the front of this document.

Sales Tel: 0844 371 1192 Fax: 01785 241818 <u>customer.service@bostik.com</u>
Technical Advice Tel: 0844 371 1197 Fax: 01785 272867 <u>technical.service@bostik.com</u>
Technical Data & COSHH (MSDS) Data Sheets Tel: 01785 272625 Fax: 01785 212962 <u>stafford.gatehouse@bostik.com</u>

